

## **Tehama Submersible MDT** Fully Potted for use in meter pits



Our IP68 rated Submersible MDT combines our MAX Range MDT with a newly designed enclosure and full epoxy encasement to provide a fully **waterproof** product. The sealed, waterproof battery enables the MDT to operate for well over 10 years in normal operation.

The submersible MDT comes in two variations, a backwards compatible version (Standard Range) that operates in any existing Tehama Network, and our new **MAX Range** version. Both variations can be ordered with either one pulse meter input or one Encoder water meter input. Meters interface to the sealed MDT wires by using waterproof IDC Splice connectors (or similar) between MDT and the Meter. Like our other MDT models, an LED provides instant feedback of the state of the MDT. A magnet waved across the side of the case replaces the button on our regular MDTs and is used to generate an instant transmission (for

field testing) and to query the device about its RF status. See Operation on next page for details.

For pit meters, the enclosure is designed to be mounting to the bottom of a plastic pit lit using screws through the two tabs, or with a waterproof adhesive. The radio range and performance of the MDT will be optimal if it is mounted to the plastic pit lid and being upside down will keep the radio within an air pocket.

## Specifications

| Inputs Options       | • Pulse input from water, electric, gas, run-time, or BTU meters |  |  |
|----------------------|--|--|--|
|                      | • Sensus/Neptune encoded protocol, or GWF Unico2coder® MP        |  |  |
| Data Resolution      | 1-hour interval  |  |  |
| Radio                | 902 – 928 MHz; FCC and IC Certified;                             |  |  |
|                      | Open field range nearly 2 miles (Compatible Models) *            |  |  |
|                      | Open field range nearly 10 miles (MAX Range Models) *            |  |  |
| LED                  | Indicates RF network connection status and on/off state          |  |  |
| Operating            | -20º to 145º F   |  |  |
| Environment          | IP68 rated, fully submersible                                    |  |  |
| Power                | Sealed primary lithium battery, 3.6V                             |  |  |
|                      |  |  |  |
| Typical Battery Life | 10+ years @ 50° to 90° F, reduced at extreme temperatures        |  |  |
| Dimensions           | 6.2″ x 2.4″ x 1.5″   |  |  |

\*Actual range may vary depending on installation location and topography. Continual product enhancements may cause specifications to change without notice.




## Models

| Submersible MDT, Pulse,<br>Standard Range       | TW-167S-P | Single pulse input counter, one-hour interval data.  |
|---|-----------|--|
| Submersible MDT,<br>Encoder, Standard Range     | TW-167S-E | Single input for Neptune/Sensus Encoder registers (auto-detecting), one-hour interval.                                   |
| Submersible MDT, GWF<br>Encoder, Standard Range | TW-167S-G | Single input for GWF Unico2coder® MP Encoder registers, one-hour interval.   |
|   |           |  |
| Submersible MDT, Pulse,<br>MAX Range            | TW-177S-P | Single pulse input counter, one-hour interval data.<br>Only for MAX Range networks                                       |
| Submersible MDT,<br>Encoder, MAX Range          | TW-177S-E | Single input for Neptune/Sensus Encoder registers<br>(auto-detecting), one-hour interval. Only for MAX<br>Range networks |
| Submersible MDT, GWF<br>Encoder, MAX Range      | TW-177S-G | Single input for GWF Unico2coder® MP Encoder registers, one-hour interval. Only for MAX Range networks                   |

\*\* Standard and MAX Range systems are NOT compatible: only MAX Range MDTs must be used with a MAX Range Repeater (and MAX Range DCAP) and vice versa. Refer to AN-119 in the documents section of our website for more information.

## Operation

The Submersible MDT operates exactly like our regular MDT. A button press is created by waving a magnet near the areas shown. Status and control are the same as our regular MDTs, including a "press" to initiate a read and transmit it to the DCAP. The LED on the top provides the same feedback as on our regular MDTs.



Tehama Wireless 2607 7th Street, Suite G Berkeley, CA 94710 415.495.7344 info@TehamaWireless.com www.TehamaWireless.com

©2020 Tehama Wireless Design Group Rev.2001