

DIRECTIONS FOR USE

1/8" MPT x 1/4"

The inlet, or left port of the solenoid already has a filter strainer within the body, so you can use the sleeve and cap from the 1/8" MPT x 1/4" compression fitting to complete the connection.

Use two wrenches on both fittings to back out the existing outlet or right side fitting, to interchange with the general replacement 5/16" compression fitting or the Honeywell® replacement barbed connection.

UHS24 Universal Humidity Solenoid 24V 687152213306

UHS120 Universal Humidity Solenoid 120V 687152213313